

PROTECTIVE COVER FOR MP 277 10" TOUCH UP TO PRODUCT VERSION "ES 14" THIN CLIENT 10" UP TO "ES 03" (6AV6646-0AA21-2AX0) WITH NARROW FRAME AMOUNT: SEE TECHNICAL DATA



<b>Product type designation</b>	
<b>Installation type/mounting</b>	
Mounting in portrait format possible	Yes
Mounting in landscape format possible	Yes
<b>Degree and class of protection</b>	
IP (at the front)	IP65
<b>Standards, approvals, certificates</b>	
CE mark	Yes
<b>Ambient conditions</b>	
<b>Ambient temperature in operation</b>	
• Min.	0 °C
• max.	50 °C
<b>Storage/transport temperature</b>	
• Min.	-20 °C
• max.	60 °C
<b>Relative humidity</b>	
• Operation, max.	95 %
<b>Mechanics/material</b>	
<b>Material of housing</b>	
• plastic	Yes
<b>Dimensions</b>	
Width	355.8 mm

Height	294 mm
Thickness	7.8 mm
Mounting cutout, width	310 mm
Mounting cutout, height	248 mm

#### Weights

Without packaging	750 g
-------------------	-------

#### Scope of supply

Number of sets	2; 2 cover frames, 2 base frames, 2 protective covers
----------------	---

#### other

Note:	for MP 277 10" Touch up to product version "ES 14 ", Thin Client 10" up to "ES 03" (6AV6646-0AA21-2AX0) with narrow frame
-------	---

Usable in the following products	
• Product 1	<a href="#">6AV6643-0CD01-1AX0</a>
• Product 2	<a href="#">6AV6643-7CD00-0CJ0</a>
• Product 3	<a href="#">6AV6643-7CD00-0CJ1</a>
• Product 4	<a href="#">6AV6643-0CD01-1AX1</a>
• Product 5	6AV6643-8*

**last modified:** 12.03.2015