

DIE SELECTION GUIDE FOR B35-45D

Copper Tube Connectors

Copper Conductor sqmm Low str. Flex.		Connector		Hexagonal Crimp		Indent Crimp		
		Terminal Lug	Through Connector	Die Set	No. of Crimps*	Nest	Indentor	No. of Crimps*
4 - 6		A1-M	L1-M	ME1	1	MA1	PA1	1
10		A2-M A2-P12	L2-M	ME2	1	MA2.3	PA5	1
16		A3-M A3-P14	L3-M	ME3	1			1
25		A5-M A5-P16	L5-M	ME5	1			MA5
35	25 35	A7-M A7-P20	L7-M	ME7	1	MA7	PA10	1
	35	A9-M		ME9	1	MA9		1
50	50	A10-M A10-P25	L10-M	ME10	2	MA10		1
	50	A12-M		ME12	2			
70	70	A14-M A14-P30	L14-M	ME14	2			
	70	A17-M		ME17	2			
95	95	A19-M	L19-M	ME19	2			
	95	A20-M		ME20	2			
120	120	A24-M	L24-M	ME24L	2			
	120	A29-M		ME29	3			
150	150	A30-M	L30-M	ME30L	3			

* No. of Crimps per end for Through Connectors

Further assistance from Cembre Ltd
Tel: 01675 470440 Fax: 01675 470220 E-mail: sales@cembre.co.uk

DIE SELECTION GUIDE FOR HT 45-E

Copper Tube Connectors

Copper Conductor sqmm Low str. Flex.		Connector		Hexagonal Crimp		Indent Crimp		
		Terminal Lug	Through Connector	Die Set	No. of Crimps*	Nest	Indentor	No. of Crimps*
4 - 6		A1-M	L1-M	ME1	1	MA1	PA1	1
10		A2-M A2-P12	L2-M	ME2	1	MA2.3	PA5	1
16		A3-M A3-P14	L3-M	ME3	1			1
25		A5-M A5-P16	L5-M	ME5	1			MA5
35	25 35	A7-M A7-P20	L7-M	ME7	1	MA7	PA10	1
	35	A9-M		ME9	1	MA9		1
50	50	A10-M A10-P25	L10-M	ME10	2	MA10		1
	50	A12-M		ME12	2			
70	70	A14-M A14-P30	L14-M	ME14	2			
	70	A17-M		ME17	2			
95	95	A19-M	L19-M	ME19	2			
	95	A20-M		ME20	2			
120	120	A24-M	L24-M	ME24	2			
	120	A29-M		ME29	3			
150	150	A30-M	L30-M	ME30	3			

* No. of Crimps per end for Through Connectors

Further assistance from Cembre Ltd
Tel: 01675 470440 Fax: 01675 470220 E-mail: sales@cembre.co.uk