


Part number
CGFA 10



Brief description:

100A CG contacts, silver plated, 8-10mmq, AWG 8-7

| | | | |
|----------------------------------|--|-------------------------------------|---|
| Product description | | Approvals / Standards | |
| Model | female contacts | Quality mark |  DNV GL, BV, EAC |
| Version | Crimp contacts CLASS series | Conformity | CQC, CE |
| Series | 100A CG contacts | General ordering information | |
| Family | crimp contacts | EAN13 code | 8015747091114 |
| N. of poles | 1 pole | Tariff number | 85369095 |
| Technical data | | Packaging Information | |
| Current | 100 A | Sub-packaging length | 1,00 mm |
| Wire cross-section | 8,00 mm ² - 10,00 mm ² | Sub-packaging height | 1,00 mm |
| AWG size | 8 - 7 | Sub-packaging width | 1,00 mm |
| Contact type | silver plated | Sub-packaging weight | 0,46 kg |
| Further technical details | | Sub-packaging description | Plastic box |
| Weight | 15,40 g | Sub-packaging quantity | 30 Pcs |
| | | Sub-packaging EAN barcode | 8015747091190 |

Part number

CGFA 10



Catalogue drawings

CGF and CGM

