

# Han B Hood Side Entry 4 Pegs PG 21



Part number	09 30 016 0520
Specification	Han B Hood Side Entry 4 Pegs PG 21
HARTING eCatalogue	https://b2b.harting.com/09300160520

Image is for illustration purposes only. Please refer to product description.

## Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> B
Type of hood/housing	Hood
Туре	High construction

## Version

Size	16 B
Version	Side entry
Cable entry	1x Pg 21
Locking type	Double locking lever
Field of application	Standard hoods/housings for industrial connectors

# Technical characteristics

Limiting temperature	-40 +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 IP66 IP67
Type rating acc. to UL 50 / UL 50E	4 4X 12

## Material properties

Material (hood/housing)	Aluminium die-cast
· · · · · · · · · · · · · · · · · · ·	



# Material properties

Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3)
	R7 (HL 1-3)

# Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

## Commercial data

Packaging size	1
Net weight	223 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140045934
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors