

SCSC clamping holder, positive, right

For longitudinal turning with CC indexable insert

ATORN[®]

Application


For longitudinal turning with CC indexable insert, 80°

Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 45°, tip angle 90°, clearance angle 7°

Advantage

- Robust geometry for longitudinal turning
- positive body geometry ensures low cutting forces



Art. no.	17830 843
ISO name	SCSC R/L 2020 K12
Shaft height	20 mm
Shank width	20 mm
Length	125 mm
Length of head	24 mm
Programming size	25 mm
Suitable for indexable inserts	CC.. 1204..
Tool design	Left

EAN-Code

4050293562910