

System trolley CONNECT Model 354

Desk, hanging cabinet and perforated metal plate wall



Execution:

- Mobile base trolley, consisting of 2 sectional supports and pushing handle
- Tray base single-sided—depth 450 mm
- Assembly of the attachment elements possible without tools in the 50 mm grid
- 1 x perforated metal plate wall, width x height 720 x 600 mm, with 10 x 10 mm square holes and 38 mm axis distance
- 1 x plastic-coated worktop, width x depth x height 830/1000 x 500 x 28 mm
- 1 x suspended cabinet with hinged doors, lockable, width x depth x height 760 x 330 x 450 mm
- Incl. 4 steering rollers (diameter 125 mm), 2 of which have locking devices
- Delivery: ready mounted, rollers unmounted

Delivery:

Ready mounted, rollers unmounted.



Art. no.	50240 660
Brand	ANKE
Model	CVM 354
Width	800 mm
Depth	450 mm
Height	1950 mm
Design	One side
Load-carrying capacity	200 kg
Load-carrying capacity of storage area	30 kg
Load-carrying capacity of base plate	100 kg
Distance between centre of hole and centre of hole	38 mm
Number of steering rollers	4 PCS
Wheel diameter	125 mm
With wheel lock	Yes
With sliding handle	Yes
Material	Sheet steel
Colour of trolley	Light grey RAL 7035
Colour of perforated panel	Anthracite grey RAL 7016
Colour of front	Anthracite grey RAL 7016
Surface	Powder-coated
Gross Weight	75.956 kg
Product Group	502