

VDE-insulated heavy-duty side cutters with 2-component grip cover

Chrome-plated steel surface, polished



Application:

For cutting wires and cables.

Execution:

- Chrome-vanadium heavy-duty steel, forged, oil-hardened
- Precision blades also inductively hardened for all types of wires
- VDE type according to DIN EN 60900

Advantage:

- Safe, ergonomic and fatigue-free working thanks to two-component handles
- With forged articulated axis for extreme, long-lasting use
- Optimum coordination of cutting angle, transmission ratio and ergonomic handle shape ensure an excellent cutting rate with little force needed
- 20% less force required compared to standard side-cutters



Art. no.	53095 740
Brand	KNIPEX
Manufacturer Part Number	74 07 250
Length	250 mm
Surface	Chrome plated
VDE certified	Yes
Max. medium wire diameter cutting capacity	4.5 mm
Material of handle	Polyvinyl chloride
Gross Weight	0.512 kg
Product Group	535

EAN

4003773018421