

64275 AX

Low-voltage halogen lamps without reflector

Areas of application

- Lamps for special luminaires
- Medical fiber optics (HLX)



Product benefits

- Compared to standard lamps up to 10 % higher luminous efficacy (HLX)
- Instant light (HLX)

Product features

- Xenon instead of krypton as the filler gas (XENOPHOT HLX versions)
- Luminous flux up to 10 % higher with same power consumption (XENOPHOT HLX versions)
- HLX tungsten halogen low-voltage lamp with or without reflector
- Dimmable (HLX)



Technical data


Electrical data

Nominal voltage	6 V
Nominal wattage	35.00 W

Photometrical data

Color temperature	3350 К
Nominal luminous flux	755 lm

Dimensions & weight





Diameter	9 mm
Length	35.0 mm
Light center length (LCL)	26.0 mm ¹⁾
Filament length	1.30 mm
Illuminated field	1.3*1.6 mm²
Filament diameter	1.6 mm

¹⁾ ±0.3 mm

Lifespan

Lifespan	50 h
Elicopuli	50 11

Additional product data

Base (standard designation)	G4
Minimum diameter of lamp enclosure	9 mm

Capabilities

Dimmable	Yes
Burning position	Any

Certificates & standards

EEI – Energy Label	C

Country specific categorizations

LIF	M/137
Order reference	64275 AX 35W 6V

Country specific information

Product code	METEL code	SEG-No.	STK-Number	UK Org
4050300258690	OSRH6427540	-	-	-
4050300258690	OSRH6427540	-	-	-



Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4050300258690	64275 AX	Folding carton box 1	25 mm x 23 mm x 70 mm	0.04 dm ³	2.00 g
4050300890913	64275 AX	Shipping carton box 40	144 mm x 107 mm x 121 mm	1.86 dm³	221.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.