

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LL 07/02/06'	~	LJC 07/02/06'
B	ADD P/N CODE	LJC 12/12/13'	~	LJC 12/12/13'
C	ADD BEND TYPE	JLZ 12/30/14'	~	

NOTES:


1. SPECIFICATIONS:

- 1.1 CONTACT RESISTANCE: 20mΩ Max.
- 1.2 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC FOR 1 MINUTE.
- 1.3 INSULATION RESISTANCE: 1000MΩ Min.
- 1.4 OPERATING TEMPERATURE: -40°C~+105°C.
- 1.5 MALE PIN RANGE: $\phi 0.381 \sim 0.635$.
- 1.6 CURRENT RATING: 3A Per Pin Max.

2. PRODUCT NUMBER CODE:

DS1002-01 - X X X X X - X


- CLIP TYPE[ⓑ]
- JK: IMPORT
- GC: DOMESTIC
- Bend Type(Single Row Only) [ⓒ]
- A: R1 Type
- B: R2 Type
- Clip plating
- 1: Tin 150u" 2: Tin 200u"
- 3: G/F 4: Gold 3u"
- 5: Gold 10u" 6: Gold 15u"
- Pin plating
- 1: Tin 150u" 2: Tin 200u"
- 3: G/F 4: Gold 3u"
- 5: Gold 10u" 6: Gold 15u"
- Mounting type
- V: V/T TYPE
- R: R/A TYPE
- S: SMT TYPE
- No. of contacts
- 1*1 - 1*64
- 2*1 - 2*40



Dual rows

Single row


V/T TYPE



Dual rows

Single row

R/A TYPE



Dual rows

Single row


SMT TYPE

N: No. of contacts

GENERAL TOLERANCE		ANGLE TOLERANCE	
X.	±0.60	X.	±5°
.X	±0.38	.X	±3°
.XX	±0.25	.XX	±2°

DRAWING TYPE	CUSTOMER		
SCALE	1:1	SHEET	10F1
DRAWING NO.	C-DS1002-01-XXXX-X-C		

PROJECTION	TITLE	2.54mm IC SOCKET(Machine Pin)	
UNITS	mm	R/A, V/T & SMT Type	
SHEET SIZE	A4	SERIES	DS1002-01 SERIES

 晨翔电子有限公司
CONNFLY[®] CONNFLY ELECTRONIC CO., LTD

CONNFLY
Tel: 86-574-63508787
Fax: 86-574-63510817
E-mail: sales@connfly.com
http://www.connfly.com
Add: East Industry Zone KuangYan
Town Cixi Ningbo China
P.O. 315333