

# Kraftsteckschlüssel 1/2"



1/2" Kraftsteckschlüssel dünnwandig - normal						
Artikelnr.	SW mm	Zeichnung	D1 mm	D2 mm	L mm	L2 mm
<b>Metrisch</b>						
12-008-D	8	A	14	22	38	9
12-009-D	9	A	14,5	22	38	12
12-010-D	10	A	15,5	22	38	12
12-011-D	11	A	16,7	22	38	12
12-012-D	12	A	18	22	38	12
12-013-D	13	A	19,2	24	38	12
12-014-D	14	A	21	24	38	12
12-015-D	15	A	21,7	24	38	12
12-016-D	16	A	23	24	38	12
12-017-D	17	B	24	24	38	13
12-018-D	18	B	25	25	38	13
12-019-D	19	B	26	26	38	13
12-020-D	20	B	27,5	27,5	38	13
12-021-D	21	B	28	28	38	13
12-022-D	22	B	29,5	29,5	38	13
12-023-D	23	B	30,5	30,5	38	13
12-024-D	24	B	32	32	45	20
12-025-D	25	B	33	33	45	20
12-026-D	26	B	35	35	50	22
12-027-D	27	B	36	36	50	22
12-028-D	28	B	37,5	37,5	50	22
12-029-D	29	C	38,5	38	50	22
12-030-D	30	C	40	38	50	22
12-031-D	31	C	41	38	50	22
12-032-D	32	C	42	38	50	22

1/2" Kraftsteckschlüssel dünnwandig - lang						
Artikelnr.	SW mm	Zeichnung	D1 mm	D2 mm	L mm	L2 mm
<b>Metrisch</b>						
12-008L-D	8	A	14	22	78	13
12-009L-D	9	A	14,5	22	78	14
12-010L-D	10	A	15,5	22	78	14
12-011L-D	11	A	16,7	22	78	14
12-012L-D	12	A	18	22	78	14
12-013L-D	13	A	19,2	24	78	14
12-014L-D	14	A	21	24	78	17
12-015L-D	15	A	21,7	24	78	17
12-016L-D	16	A	23	24	78	17
12-017L-D	17	B	24	24	78	17
12-018L-D	18	B	25	25	78	17
12-019L-D	19	B	26	26	78	19
12-020L-D	20	B	27,5	27,5	78	19
12-021L-D	21	B	28	28	78	24
12-022L-D	22	B	29,5	29,5	78	24
12-023L-D	23	B	30,5	30,5	78	24
12-024L-D	24	B	32	32	78	24
12-025L-D	25	B	33	33	78	24
12-026L-D	26	B	35	35	78	24
12-027L-D	27	B	36	36	78	24
12-028L-D	28	B	37,5	37,5	78	24
12-029L-D	29	C	38,5	38	78	54
12-030L-D	30	C	40	38	78	54
12-031L-D	31	C	41	38	78	54
12-032L-D	32	C	42	38	78	54

