

Datasheet

RS Pro Straight 50 Ω PCB Mount BNC Connector, jack, Solder Termination

RS Stock No: **526-0279**



Product Details

RS Pro straight PCB mount BNC connector features brass construction with nickel and gold plated contacts. This female connector has 50 Ω impedance. It operates at a voltage rating of 335 V and temperature rating of -65 to +85°C at a frequency of 0 to 1 GHz.

Features and Benefits

- Brass construction with nickel and gold plated contacts
- Solder termination method
- Female connector

Specifications:

Body Orientation	Straight
Body Plating	Nickel
Contact Material	Phosphor Bronze
Contact Plating	Gold
Gender	Female
Impedance	50 Ω
Mounting Type	PCB Mount
Operating Frequency	0 to 1 GHz
Polarity	Normal
Termination Method	Solder
Contact Resistance	1.5 m Ω (Maximum Central), 0.5 m Ω (Maximum Outer)
Insulation Material	PTFE (Internal)
Insulation Resistance	5000 M Ω
Number of Functions	500
Operating Temperature Range	-65 to +85°C
Voltage Rating	750 V (Insulation), 335 V (Working)