



Sample image

**Order symbol:** TA292411

**Product nbr:** 5814003

**Description:** Enclosure. ABS


**Remarks:** Opaque cover

**Including:** Base with PUR gasket and screws for mounting plate/DIN-rail. cover with polyamide cover screws and plastic hinges.

**EAN:** 6418074060754

**EI. number:**

- Finland: 3435688
- Denmark: 8212035069
- Sweden: 5814003



**Dimensions:** Height Width Depth

mm: 289 239 107

inch: 11.38 9.41 4.21

**Accessories:**

MP 2924 Mounting plate. for enclosures:

DR 215 DIN-35 Mounting rail. for enclosures:  
(215 x 35 x 1)

DR 265 DIN-35 Mounting rail. for enclosures:

**Materials:**

Material: ABS

Base colour:

Cover colour:

Gasket material:

**Temperatures:**

Temperature °C (short term):: -40 ... 80

Temperature °C (continuous):

Temperature °F (short term): -40 ... 175

Temperature °F (continuous): -40 ... 140

(265 x 35 x 1)

FP 10674 Mounting foot kit (2 pcs) incl. screws

**Rating:**

Ingress protection (EN 60529): IP65;

Impact Resistance (EN 62262): IK07;

Electrical insulation: Totally insulated

Halogen free (DIN/VDE 0472, Part 815): 1

UV resistance: -

Flammability Rating: UL 94 HB

Glow Wire Test (IEC 695-2-1) °C: 650 °C

NEMA Class

**Certificates:**

Certificate FI 40343