


FT-30-P-A-R8

Fibre optics



Product characteristics	
Diffuse reflection sensor	
Ø 8 mm	
Range 70 mm	
Connection to fibre optic amplifiers type OIF	
Range	
Range	OIF: 70 mm
Environment	
Ambient temperature [°C]	-20...80
Mechanical data	
Design	
	angled
Length [mm]	600
Min. bending radius [mm]	30
Fiber arrangement	
	⊙
Fibre optic	
	glass
Sensing head	
	aluminium
Sheathing	
	PVC; adapter: polyamide
Weight [kg]	0.088
Accessories	
Accessories (included)	E20353
Remarks	
Pack quantity [piece]	1