

M8 MALE 0° FIELD-WIREABLE (SOLDER PINS)

3-pol. 0.25mm²

Male straight


3-pole


with solder pins

Connection cross section: max. 0.25 mm²

[Link to Product](#)

Illustration





Product may differ from Image

Approvals



Form

08401

Technical Data

| | |
|--------------------------------|--|
| Operating voltage | max. 60 V AC/DC |
| Operating current per contact | max. 4 A |
| Connection cross section | max. 0.25 mm ² |
| Sealing range (cable diameter) | 3.5...5.0 mm |
| Protection | IP67 inserted and tightened (EN 60529) |

General data

| | |
|----------------------|--------------|
| Temperature range | -25...+85 °C |
| Dimensions H × W × D | 45×12×12 mm |

Commercial data

| | |
|------------------------|----------|
| country of origin | DE |
| customs tariff number | 85369010 |
| minimum order quantity | 1 |