

## M12 male 0° / M12 female 0° DeviceNet


PUR AWG24+AWG22 shielded vt UL/CSA+drag ch. 0,41m

DeviceNet, CANopen  
 Male straight to female straight  
 M12 - M12  
 5-pole, shielded

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request. Further cable lengths on request.


### [Link to Product](#)

#### Illustration



Male

Female





Product may differ from Image

### Approvals



### More Info



### Form

40531

### Technical Data

|                               |   |
|-------------------------------|---|
| Operating voltage             | max. 60 V AC/DC   |
| Operating current per contact | max. 4 A  |
| Locking of ports              | Screw thread M12 × 1 mm (recommended torque 0.6 Nm) self-securing |
| Protection                    | IP67 inserted and tightened (EN 60529)                            |

### Cables

|                             |                                 |
|-----------------------------|---------------------------------|
| Cable number                | 803                             |
| No./diameter of wires       | 2×0.25 + 2×0.34 mm <sup>2</sup> |
| Wire isolation              | PE (rd, bk), (bl, wh)           |
| C-track properties          | 5 Mio.                          |
| Jacket Color                | violet                          |
| Shore hardness outer jacket | 90 ± 5A                         |
| Material (jacket)           | PUR (UL/CSA)                    |
| Outer diameter              | approx. 6.9 mm                  |

The information in this brochure has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 05/15

|                            |              |
|----------------------------|--------------|
| Bend radius (fixed)        | 8 × outer Ø  |
| Bend radius (moving)       | 12 × outer Ø |
| Temperature range (fixed)  | -40...+80 °C |
| Temperature range (mobile) | -20...+60 °C |
| Shielded                   | yes          |

**Commercial data**

|                        |          |
|------------------------|----------|
| country of origin      | CZ       |
| customs tariff number  | 85444290 |
| minimum order quantity | 1        |