



Junction boxes, COMBI 607



COMBI 607



Protection class: IP 66 / 67
Glow wire test: 750 °C
Temperature range: -30 °C - 100 °C
Installation temperature: -5 °C - 60 °C
Voltage: 690 V
Terminals/poles: 6 mm²
Advice: Colour: RAL 7035 · .../S = RAL 9005 · .../W = RAL 9001
Material: Polypropylene, Gasket: TPE

Type	WISKA-No.	 (mm)		LxBxH external (mm)	
COMBI 607/empty	10060531	3 · 17		110 x 110 x 66	3
COMBI 607/empty/S	10060648	3 · 17		110 x 110 x 66	3
COMBI 607/empty/W	10060533	3 · 17		110 x 110 x 66	3
COMBI 607/5	10060532	3 · 17		110 x 110 x 66	3
COMBI 607/5/S	10060538	3 · 17		110 x 110 x 66	3
COMBI 607/5/W	10060534	3 · 17		110 x 110 x 66	3
DIN RAIL KIT 607	10060361	-			1

POLYAMIDE
POLYAMIDE ACCESSORIES
MEMBRANE
BRASS
BRASS ACCESSORIES
MARITIME
STAINLESS STEEL
EMC
EX E / I
EX D
VENTING
BS 6121
SEALINGS, TOOLS
JUNCTION BOXES
TECHNICS
INDEX