


CAT6A Compact shielded through coupler, DIN rail mount



Compact Shielded CAT6A through coupler, DIN rail mountable, (dustcovers included). (SGACDINS)

Features:

- Features Cat.6A/Class EA Screened Inline Coupler, RJ45 F/F
- For mounting on DIN-Rail TH35 acc. to DIN EN60715
- Side-by-side mountable
- Built in earthing spring
- Supplied with Dust Cover
- IP20
- 4PPoE compliant
- Durability: 750 jack insertion cycles

Specifications:

- Net weight (including primary packaging): 24g
Dimensions: 45mm x 18.5mm x 26 mm (as packed)
- Colour: Grey – RAL 7035

Materials

- Dust cover: Polypropylene
- Outer casing: Glass fibre reinforced polyamide
- Coupler body: Zinc alloy electroplated with nickel
- RJ45 socket contacts: 50µ"/1.27µm gold-plated phosphor bronze


Packaging: Packaged individually then bagged in 20s.

Commodity code: 85444920

EAN: 5055386510570







Country of Origin China

Illustrative images



ROHS Compliant

LIMITS	DEGREE CLASS			
	A	B	C	D
10	±0.02	±0.05	±0.10	±0.15
10-50	±0.05	±0.10	±0.15	±0.20
50-120	±0.10	±0.15	±0.20	±0.25
120-300	±0.15	±0.20	±0.25	±0.30
300-500	±0.20	±0.25	±0.30	±0.35
500-1000	±0.25	±0.30	±0.35	±0.40
1000-1500	±0.30	±0.35	±0.40	±0.45
ANGLE	±0.2°	±0.5°	±1.0°	±1.5°



ELECTRICAL

CURRENT RATING : 1.5A
 DIELECTRIC WITHSTANDING VOLTAGE : 1000VDC
 INSULATION RESISTANCE : 500 MΩ MIN.
 CONTACT RESISTANCE : 20 mΩ MAX.
 RATED TEMPERATURE: -25°C-50°C

MECHANICAL

(1) Materials:

- 1:PP HB WH01
- 2:PA66+GF FR RAL7035
- 3:SUS304 T=0.15mm
- 4:PA66+GF FR RAL7035
- 5:Zn alloy

(2) Cosmetic: Electroplating Ni + Sandblasting

(2) RJ45 Jack Contact: Phosphor bronze, 50µ"/1.27µm Gold Plating

(3) Cavity conforms to FCC rules and Regulations Part 68