



## PART NUMBERING CODES



Fair-Rite PN	Material Permeability	Ferrite Thickness	PET Thickness	Tape Thickness	Sheet Size*	Total Thickness
38M1010AA1212	20	0.1 mm	0.01 mm	0.02 mm	120 x 120 mm	0.13 mm
38M1020AA1212	20	0.2 mm	0.01 mm	0.02 mm	120 x 120 mm	0.23 mm
38M1040AA0606	20	0.4 mm	0.01 mm	0.02 mm	60 x 60 mm	0.43 mm
38M1050AA0606	20	0.5 mm	0.01 mm	0.02 mm	60 x 60 mm	0.53 mm
38M2010AA1212	45	0.1 mm	0.01 mm	0.02 mm	120 x 120 mm	0.13 mm
38M2020AA1212	45	0.2 mm	0.01 mm	0.02 mm	120 x 120 mm	0.23 mm
38M2040AA0606	45	0.4 mm	0.01 mm	0.02 mm	60 x 60 mm	0.43 mm
38M2050AA0606	45	0.5 mm	0.01 mm	0.02 mm	60 x 60 mm	0.53 mm
38M3010AA1212	60	0.1 mm	0.01 mm	0.02 mm	120 x 120 mm	0.13 mm
38M3020AA1212	60	0.2 mm	0.01 mm	0.02 mm	120 x 120 mm	0.23 mm
38M3040AA0606	60	0.4 mm	0.01 mm	0.02 mm	60 x 60 mm	0.43 mm
38M3050AA0606	60	0.5 mm	0.01 mm	0.02 mm	60 x 60 mm	0.53 mm
38M4010AA1212	120	0.1 mm	0.01 mm	0.02 mm	120 x 120 mm	0.13 mm
38M4020AA1212	120	0.2 mm	0.01 mm	0.02 mm	120 x 120 mm	0.23 mm
38M4040AA0606	120	0.4 mm	0.01 mm	0.02 mm	60 x 60 mm	0.43 mm
38M4050AA0606	120	0.5 mm	0.01 mm	0.02 mm	60 x 60 mm	0.53 mm
38M5010AA1212	140	0.1 mm	0.01 mm	0.02 mm	120 x 120 mm	0.13 mm
38M5020AA1212	140	0.2 mm	0.01 mm	0.02 mm	120 x 120 mm	0.23 mm
38M5040AA0606	140	0.4 mm	0.01 mm	0.02 mm	60 x 60 mm	0.43 mm
38M5050AA0606	140	0.5 mm	0.01 mm	0.02 mm	60 x 60 mm	0.53 mm
38M6010AA1212	220	0.1 mm	0.01 mm	0.02 mm	120 x 120 mm	0.13 mm
38M6020AA1212	220	0.2 mm	0.01 mm	0.02 mm	120 x 120 mm	0.23 mm
38M6040AA0606	220	0.4 mm	0.01 mm	0.02 mm	60 x 60 mm	0.43 mm
38M6050AA0606	220	0.5 mm	0.01 mm	0.02 mm	60 x 60 mm	0.53 mm





- M1 20 permeability ( $\mu'$ )
- M2 45 permeability ( $\mu'$ )
- M3 60 permeability ( $\mu'$ )
- M4 120 permeability ( $\mu'$ )
- M5 140 permeability ( $\mu'$ )
- M6 220 permeability ( $\mu'$ )

