



**2-Way Miniature
T&B Catalog Number:**

TC104
78621082246
Active

**UPC Number:
Status:
Description:**

Miniature Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 10.3mm (0.406 Inches), Width of 7.92mm (0.312 Inches), Height of 2.4mm (0.094 Inches), #5 Screw Mounting Method

Features

These miniature mounting bases are ideal for high-density packaging. Threaded insert permits screw to come from outside of mounting surface.

General

Material	Nylon 6.6
Color	Natural
Mounting Method	Screw
Stud Size	#5 Screw
Max Tie Width Accepted	.091
For Cable Ties	Up to 18 lbs.

Dimension Information

Length (inches)	.406
Width (inches)	.316

Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Packaging

T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	10000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	0.63 lbs. per 1000

Application Support

Material Selection Guide	Available on Website
--------------------------	----------------------

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E49405

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com