

The 120dB (A) Asserta Industrial warning sounder beacon is designed to cope with harsh environments requiring protection to IP66. Design features are incorporated to ensure safe and easy installation, while providing flexibility with fewer product variants.


Features


- Powerful 120dB(A) output
- 3 stage alarm and time out function
- 42 alarm tones
- Asymmetric beacon

Benefits

- Maximum sound output for high noise environments
- 3 levels of alarm for differing warning states
- Large range of tone options
- Efficient use of light reduces current input generating the same light output as a 5j beacon

Dimensions






Technical Specification

18 - 30Vdc 230Vac	
110dB(A) 105mA @ 24Vdc (Typical Tone 3) 120dB(A) 450mA @ 24Vdc (Typical Tone 3)	
120 - 620mA @ 24Vdc (dependant on setting)	
110dB(A) 120dB(A)	
42	
3	
3.6j @ 24Vdc 2.0j @ 230Vac	
1Hz (adjustable on 24Vdc)	
Reverse polarity (dc version)	
- 25°C to + 70°C	
IP66	
ABS, PC	
1.8Kg (dc version)	
2.5Kg (mains version)	
Red or grey	
Red, amber, blue or clear	

Asserta Sounder Beacon Grey



Catalogue Numbers

Reference	Cat No	Description
AS/SB/24/120/R/RL	7021121FUL-0004X	Asserta Sounder/Beacon 24v Red 120dB Red Lens
AS/SB/24/120/G/AL	7092275FUL-0152X	Asserta Sounder/Beacon 24v Grey 120dB Amber Lens

