

Cutting body solid carbide TiAlN for Top Drill M 1

For universal use up to 1300 N/mm²



Application:

High-performance drilling in conjunction with indexable insert drill for universal application up to 1300 N/mm²

Execution:

- Precision-ground indexable insert, tip angle 140°

Advantage:

- Simply replacement of cutting body: No screws or clamps required
- The cutting body can be replaced using a wrench, which is supplied with each tool body
- No regrinding costs
- Consistent performance from cutting edge to cutting edge



Art. no.	11224 090
Brand	WIDIA
Manufacturer Part Number	3849043
Cutting material	SC
Carbide type	WU25PD
Cutting edge diameter	9 mm
Indexable insert type	W12
Surface	TiAlN
Cutting direction	Right-hand cutting
Angle of the tip	140 Degree
Gross Weight	0.002 kg
Product Group	1XA

EAN

4021169585982