

## coolant nozzle DriveKD

For rotary tools

**RIHETEC**  
Kühlmitteldosen

### Application:

Conventional coolant nozzles, often spray in all directions and do not provide a direct coolant jet. This often results in inadequate cooling at the tool cutting edge. The DriveKD performs its task superbly well.

### Execution:

- threaded connectors M8x1, M10x1 and 1/8 thread
- internal pipe diameter 4 mm
- pipe length 50 mm or 70 mm
- max. pressure 10 bar (50 mm, 70 mm)
- special length of 100 mm available upon request (max. pressure up to 6 bar)

### Advantage:

- quick, easy installation
- Precise and strong coolant stream onto the tool cutting edge, for a long service life.
- precisely adjust the coolant stream using the flexible pipe
- reasonable price
- Broad range of uses



<b>Art. no.</b>	<b>21665 257</b>
<b>Brand</b>	RIHETEC
<b>Manufacturer Part Number</b>	7G 187
<b>Gross Weight</b>	0.019 kg
<b>Product Group</b>	278

### EAN

4260711110160