

## Hinged-door cabinet with solid sheet metal doors, width 1500 mm

With shelves

### Application:

For secure and clearly-visible storage of tools, accessories, files or many other parts.

### Execution:

- Stable welded steel sheet structure with base
- Solid sheet metal doors
- zinc-plated shelves, height-adjustable in increments of 17 mm, load capacity per shelf 80 kg with evenly distributed weight
- Inset-type doors with internal pivot pins, doors reinforced by box profile on inside, double-edged on all sides
- locks by means of a turning handle with integrated cylinder lock, includes 3 keys 2 keys

### Delivery:

Shelves with load capacity of 100 kg with evenly distributed load, DOM locking system (fits HK tool cabinets, HK tool shelves, HK workbenches) and other colours available upon request.



<b>Art. no.</b>	<b>50045 160</b>
<b>Brand</b>	PAVOY
<b>Manufacturer Part Number</b>	3 1310-150-500-7357 16
<b>Door design</b>	Full-sheet panel
<b>Width</b>	1500 mm
<b>Depth</b>	500 mm
<b>Height</b>	1950 mm
<b>Number of shelves</b>	4 PCS
<b>Load-carrying capacity per shelf</b>	80 kg
<b>Load-carrying capacity</b>	400 kg
<b>With partition wall</b>	No
<b>Central locking</b>	Yes
<b>Lock type</b>	Twist-grip lock with three-point fastening
<b>Material</b>	Sheet steel
<b>Cabinet colour</b>	Light grey RAL 7035
<b>Colour of front</b>	Anthracite grey RAL 7016
<b>Surface</b>	Powder-coated
<b>Gross Weight</b>	89.000 kg
<b>Product Group</b>	5CB