

Compact angle grinder 125 mm

With variable rotation speed



Application:

Compact angle grinders with variable speed for effective grinding and cutting work.

Execution:

- Robust motor for daily use. Long-lasting thanks to overload protection and long carbon brush service life.
- Comprehensive user protection through rebound monitoring, restart protection, soft start and anti-vibration handgrip.
- The gear head can be rotated by 90° for a wide range of applications.
- Fast, tool-free changing of abrasives: Quick-release nut included as standard.
- High overload capability thanks to direct motor cooling.
- Industrial cable H07, 4 m length.
- Flexible application options due to variable speed.
- Fast work progress thanks to powerful motor.



Art. no.	70374 004
Brand	FEIN
Manufacturer Part Number	72228060000
Model	CG 13-125 V
Manufacturer Article Number	72228060000
Battery included	No
Number of rechargeable batteries/batteries	0
Washer diameter	125 mm
Power input	1300 W
Power output	700 W
Idle speed	11500 rpm
Thread dimension of spindle	M14
Weight	2.3 kg
With restart protection	Yes
With soft start	Yes
With overload protection	Yes
With electronic feedback	No
With reverse switch off	Yes
With speed control	Yes
With disc brake	No
With quick clamping system	No
With dead man function	No
Sound-pressure level	91 dB
Noise level	102 dB
Gross Weight	2.300 kg
Product Group	704

EAN

4014586895000