



GE
Lighting



Double Ended Quartzline

P2/27 FEX 230V

88482

Product information

Precision range of double ended Quartzline® lamps widely used in theatre and many other applications. A range from 350 W to 2,000 W with 3200K.



Product data

EAN Code	0043168884822
DUN Code	10043168884829
Bulb Shape	Tubular
Bulb Diameter [mm]	26.5
Cap/Base	Rx7s
Dimming Capability	Yes
Gross weight per piece [g]	89
Maximum Overall Length [mm]	143
Net weight per piece [g]	44
Brand	General Electric (GE)

Performance data

Nominal power [W]	2000
Nominal lamp voltage [V]	230
Nominal lumens [lm]	50000
Nominal correlated colour temperature (CCT) [K]	3200
Rated Life [h]	300
Ballast Required	NO
Coil type	C8
Energy efficiency class (EEC)	C
Weighted energy consumption [kWh/1000h]	1965.54

Logistic data

Pack Quantity	12
Pallet quantity EUR (PC)	1152
Pallet quantity UK (PC)	1440
Inner pack type	BOX
Outer pack type	OUTER BOX
Outer case size	350 x 190 x 134 (mm)
Layer quantity	144 EUR, 180 UK
Layer quantity EUR	144
Layer quantity UK	180
Product status	Available

Application areas



Theatre

Downloads & Links

[Go to the catalog site \(HTTP\)](#)[Entertainment Solution Spectrum Catalogue \(PDF\)](#)[Lighting design tools & calculators \(HTTP\)](#)

Disclaimer

Special Purpose Lamp, Not suited for household illumination