





Medical / Incandescent

	Type SI7612 12V 50W BA20d
	Ordering - No. 67612
Product Description	Special Incandescent Lamp
Features	Softglass Bulb, Exactly positioned Filament
Applications	Medical, Microscope, Analysis, Projection

Technical Details	
Type	SI7612
Rated Voltage (V)	12
Wattage (W)	max. 55
Luminous Flux (lm)	1150 -12%
Average Lifetime (h)	50
Base	BA20d
Overall Length (mm)	max. 64,0
Bulb Diameter (mm)	max. 35,0 ± 1,0
Light Center Length (mm)	30,0 ± 0,5
Operating Position	optional
Packaging Configuration	100 pcs.
Environmental Remark	Product don't contain lead or mercury and is conform with Directive 2002/95/EC "Restriction of the use of certain hazardous substances in electrical and electronic equipment".

Drawing (in mm)



valid from	05.03.2014—V2—PN14/0072
replace for	29.01.2013—V1
file	67612.100.pdf