



# 69001-728 STECKVERBINDER R, EN 60603, DIN 41612, FEDERLEISTE, 96 KONTAKTE, LÖTSTIFTE, 3 MM



## KEY FEATURES

Anforderungsstufe 2 nach EN 60603-2, (DIN 41642)

Codierung separat bestellen

## PRODUKTMERKMALE

Produkttyp: Steckverbinder

Typ: Federleiste

Passend zu: Front-Platten

Anzahl Kontakte: 96

Kontaktfläche: Hartvergoldet

Anschlussraster 2,54 mm

Kriechstrecken Kontakt-Kontakt [mm]: 1,2 mm

Luftstrecke Kontakt-Kontakt [mm]: 1,2 mm

Max. Strom bei 20°C: 2-A

Max. Widerstand: 20 mΩ

Max. Steck- und Ziehkräfte [N]: 60 N

Prüfspannung Ueff Kontakt-Kontakt [kV]: 1 kV

Prüfspannung Ueff Kontakt-Masse [kV]: 1,55 kV

Reihenzuordnung: A; B; C

## ZUSÄTZLICHE PRODUKTDDETAILS

DIN-Steckverbinder/-Buchse Bauform R. Anforderungsklasse 2 nach EN 60603 (DIN 41642).

## ZERTIFIZIERUNGEN



### Nordamerika

All locations  
+1.763.422.2661  
Chat with us:  
[schroff.nvent.com](https://schroff.nvent.com)

### Europa

Straubenhardt, Deutschland  
+49.7082.794.0  
Betschdorf, Frankreich  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[schroff.nvent.com](https://schroff.nvent.com)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, Volksrepublik  
China  
+86.532.8771.6101  
Singapur  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[schroff.nvent.com](https://schroff.nvent.com)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, Indien  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[schroff.nvent.com](https://schroff.nvent.com)



Our powerful portfolio of brands:  
[nVent.com](https://nVent.com) **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2023 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.