## **Product Specification PDF**



| Date              | Correct as of 12th May 2020                         |
|-------------------|-----------------------------------------------------|
| Brand             | C.K                                                 |
| Product           | T3780DEF 110                                        |
| Description       | SensoPlus ESD Side Cutter Extra Full Flush<br>110mm |
| Barcode           | 5013969687613                                       |
| Commodity code    | 8203200000                                          |
| Country of origin | DE                                                  |



Features & Benefits ~ Special alloy steel, drop forged, hardened & tempered for exceptional strength & durability ~ Precision box

joint construction for permanent, adjustment free jaw alignment ~ Induction hardened jaws for outstanding long term performance ~ Mirror polished surface eliminates the risk of damage from flaking chrome ~ Spot welded double leaf springs for consistent, repetitive action ~ Ergonomically designed dual component handles for increased comfort & control ~ Fully ESD compliant for safe use on sensitive electronic components ~ According to IEC 61340 5.1 & 5.2 ~ Tapered head ~ Bevel: Extra Full Flush Cut ~ Length of cutting edges: 9 mm ~ Overall length: 120 mm ~ Cutting capacities wire: Hard: ~ mm / Medium Hard: 0,6 mm / Soft: 1,0 mm

Applicable Standards IEC 61340 5.1 & 5.2

None applicable

Health & Safety

Warranty C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through

normal wear and tear or resulting from inappropriate use, is not covered.

| Product Weights and Measures |              |                             |                     |                   |  |
|------------------------------|--------------|-----------------------------|---------------------|-------------------|--|
|                              | Product only | Product & primary packaging | Secondary packaging | Transit packaging |  |
| Item Quantity                | 1            | 1                           | 0                   | 120               |  |
| Width mm                     | 75           | 57                          | 0                   | 380               |  |
| Depth mm                     | 6            | 25                          | 0                   | 300               |  |
| Height mm                    | 120          | 160                         | 0                   | 360               |  |
| Weight                       | 57           | 76                          | 0                   | 9.8               |  |
| Packaging Information        | Card use     | Box                         | 0                   | Case              |  |
|                              | Card gms     | 18                          | 0                   | 675               |  |
|                              | Plastic use  | Bag                         | 0                   | -                 |  |
|                              | Plastic gms  | 1                           | 0                   | -                 |  |
|                              | Metal use    | 0                           | 0                   | -                 |  |
|                              | Metal gms    | 0                           | 0                   | 0                 |  |
|                              | Timber use   | 0                           | 0                   | -                 |  |
|                              | Timber gms   | 0                           | 0                   | 0                 |  |