


FE-30-A-A-M6/3M

Fibre optics



Product characteristics

Through-beam sensor

M6

Sensing range 192 mm

Connection to fibre optic amplifiers type OIF

Range

Sensing range	OIF: 192 mm
---------------	-------------

Environment

Ambient temperature [°C]	-40...290
--------------------------	-----------

Mechanical data

Design	straight
--------	----------

Length [mm]	3000
-------------	------

Min. bending radius [mm]	30, for fixed installation
--------------------------	----------------------------

Fiber arrangement



Fibre optic

glass

Sensing head

aluminium

Sheathing

aluminium; adapter: polyamide

Weight [kg]	0.273
-------------	-------

0.273

Accessories

Accessories (included)	2 hexagon nuts; M6; stainless steel; 2 tooth lock washers; 1 knurled nut; M30
------------------------	---

Remarks

Pack quantity [piece]	1
-----------------------	---