

POWER DISTRIBUTOR PD4 PLUG 24+E

Connector for 27680 and 27681

Industry female plug 24+PE
Field-wireable

[Link to Product](#)

Illustration



Product may differ from Image

Technical Data

Operating voltage	50 V AC/120 V DC (SELV)
Operating current per contact	max. 9 A
Protection	IP67 inserted and tightened (EN 60529)
Housing	Aluminum die-cast (powder-coated)
Connection cable	0.5...2.5 mm ² (AWG 20...12)
Sealing range (cable diameter)	9...17 mm

General data

Temperature range	-30...+85 °C
Dimensions H × W × D	120×43×70 mm

Commercial data

country of origin	DE
customs tariff number	85366990
minimum order quantity	1