

SRDC insert holder, positive neutral

For copy and longitudinal turning with RC indexable insert

WIDIA 

Application:

For copy and longitudinal turning with RC indexable insert

Execution:

- Precision-manufactured steel support burnished, hardened, type R

Advantage:

- Streamlined geometry, optimised for contour lathe work
- Positive body geometry ensures low cutting forces



Art. no.	17684 130
Brand	WIDIA
Manufacturer Part Number	3879736
ISO name	SRDC N 2020 K10
Shaft height	20 mm
Shank width	20 mm
Length	125 mm
Length of head	20 mm
Programming size	16.5 mm
Suitable for indexable inserts	CN.. 1204..
Tool design	Neutral
Gross Weight	0.385 kg
Product Group	1XG

EAN

4021169809613