

## Surface chuck (Weldon)

In accordance with ISO 7388-1 (DIN 69871) with resealable cooling duct bores

**ORION**<sup>®</sup>

### Application:

for clamping tools with straight shanks and clamping surfaces in line with DIN 1835 B.

### Execution:

- All tapers and tolerances are precision-ground.
- Taper tolerance AT3.
- Strength HRC 57-60.
- Core strength 1,000-1,200 N/mm<sup>2</sup>.
- KKB= resealable coolant bores

### Advantage:

- Prevents the tool from slipping while maintaining high concentricity.

### Delivery:

1x surface chuck (Weldon) in accordance with ISO 7388-1 (DIN 69871) with resealable cooling duct bores.



<b>Art. no.</b>	<b>23157 313</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	23157313
<b>Tool holding device</b>	SK 40
<b>Clamping diameter</b>	14 mm
<b>Projecting length</b>	50 mm
<b>Outer diameter</b>	44 mm
<b>Coolant supply</b>	KKB
<b>Balancing quality</b>	G 2.5 at 25 rpm
<b>Form</b>	AD/AF
<b>Thread dimension</b>	M12
<b>Gross Weight</b>	1.147 kg
<b>Product Group</b>	2AV

### EAN

4053625398331