

## Workbench trolleys

Working height 840 mm, with 2 loading surfaces

### Application:

The mobile workstation with versatile options for use.

### Execution:

- Welded sheet steel construction equipped with one workbench top panel made of solid beechwood, 40 mm thick

### Advantage:

- When you buy this product, you plant a tree and also receive a tree certificate!
- When you buy this product, you plant a tree and also receive a tree certificate!



<b>Art. no.</b>	<b>50285 205</b>
<b>Brand</b>	HK
<b>Manufacturer Part Number</b>	50285205
<b>Number of fixed rollers</b>	2 PCS
<b>Working height</b>	840 mm
<b>Number of steering rollers</b>	2 PCS
<b>Worktop width</b>	1150 mm
<b>Worktop height</b>	40 mm
<b>Worktop depth</b>	700 mm
<b>On castors</b>	Yes
<b>Moving device, can be lowered</b>	No
<b>Cabinet colour</b>	Optional
<b>Surface</b>	Powder-coated
<b>With wheel lock</b>	Yes
<b>Load-carrying capacity</b>	820 kg
<b>Wheel diameter</b>	200 mm
<b>Type</b>	mobile
<b>Material of worktop</b>	Solid beech
<b>Material</b>	Sheet steel
<b>Material of wheel</b>	Solid rubber
<b>Gross Weight</b>	61.000 kg
<b>Product Group</b>	501

### EAN

4039247470617