

Pneumatic straight grinder G 232 H

**MANNESMANN
DEMAG**

Application:

For heavy deburring work as well as high-precision milling, grinding and roughing

Delivery:

Includes hose unit and collet chuck keys



Art. no.	75061 080
Model	G 232 H
Valve design	Lever valve
Max. idle speed	25000 rpm
Min./max. idle speed	0-25000 rpm
Power output	440 W
Air consumption	12 l/s
Connection thread	G 1/4 inch
Sound-pressure level	76 dB
Length	180 mm
Diameter of housing	39 mm
Collet chuck diameter	6 mm
Suitable for max. sanding block diameter	24 mm
Max. HM rotating milling cutter diameter	12 mm
Weight	0.74 kg

EAN-Code

4251757300325