



800
kWh/1000h

B
energy class

25
lumens/watt

Double Ended Quartzline DXX 800-T4-4CL 240V 36953

Product information

Precision range of double ended Quartzline® lamps widely used in theatre and many other applications. A range from 350 W to 2,000 W with 3200K.

Application areas

 Theatre



Product data

Product Code	36953
Bulb Shape	Tubular
Bulb Diameter [mm]	15
Maximum Overall Length [mm]	80
Net weight per piece [g]	102
Gross weight per piece [g]	104
Brand	GE Lighting
Cap/Base	R7s

Performance data

Rated Lumens [lm]	20000
Weighted energy consumption [kWh/1000h]	800.0
Energy efficiency class (EEC)	B
Rated Life [h]	75
Nominal correlated colour temperature (CCT) [K]	3200
Nominal lumens [lm]	20000
Colour Rendering Index (CRI) [Ra]	100

Electrical data

Rated power [W]	800.0
Coil type	CC-8
Dimming Capability	Yes
Ballast Required	No
Nominal power [W]	800.0
Nominal lamp voltage [V]	240

Logistic data

DUN Code	00043168369534
EAN Code	0043168369534
Pack Quantity	24
Layer quantity	576 EUR, 792 UK
Layer quantity EUR	576
Layer quantity UK	792
Pallet quantity EUR (PC)	3456
Pallet quantity UK (PC)	4752
Outer case size	249 x 141 x 162 (mm)
Product status	Available

Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[Entertainment Solution Spectrum Catalogue \(PDF\)](#)

[Lighting design tools & calculators \(HTTP\)](#)

[Lighting design tools & calculators \(HTTP\)](#)

[Entertainment Pocket brochure \(PDF\)](#)

[High-res images / Technical drawings \(HTTP\)](#)

[Certificate for the Quality Management System of GE Lighting EMEA \(PDF\)](#)

[Certificate for the Environmental Management System of GE Lighting EMEA \(PDF\)](#)

Disclaimer

Special Purpose Lamp, Not suited for household illumination

