



Part Number : [192030063](#)

Product Description : VersaKrimp Temp-Term Ring Tongue Terminal for 14 to 16 AWG Wire, Stud Size 10 (M5)

Series Number : 19203

Status : Active

Product Category : Ring and Spade Terminals

Engineering Number : BB-T-337-10



---

## Documents & Resources

### Drawings

[Drawing 192030063\\_sd.pdf](#)

### Specifications


[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-013-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Ring and Spade Terminals
Series	19203
Description	VersaKrimp Temp-Term Ring Tongue Terminal for 14 to 16 AWG Wire, Stud Size 10 (M5)
Comments	650° F (343° C)
Keyword	Ring Terminal, Ring Terminals
Product Family	High-Temperature Temp Terms Terminals and Splices
Product Name	Temp-Terms,VersaKrimp
Type	Ring
UPC	800755059311

### Agency

UL	E32244
----	--------

### Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.620/g
Packaging Type	Bag
Stud Size	10 (M5)
Wire Size (AWG)	14, 16
Wire Size mm <sup>2</sup>	1.00-2.50

---

### Application Tooling

## Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm <sup>2</sup> - 0.5mm <sup>2</sup>	<u>0640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>0640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>0640160038</u>

---

This document was generated on Sep 26, 2023