



**SPECIFICATIONS:**

1. CONTACT RESISTANCE: 20m OHM MAX.
2. INSULATION REISTANCE: 300M OHM MIN. AT DC 500V.
3. VOLTAGE WITHSTANDING: AC 1000V FOR ONE MIN.
4. INSERTION FORCE: 4.0KG MAX.
5. WITHDRAWAL FORCE: 1-3.5KG.

**MATERIALS:**

- 1.SOCKET CASE:SPCC-SD 0.4t  
NICKEL PLATED
- 2.INSULATOR:P.B.T
- 3.EARTH TERMINAL:PBSR-H 0.25t
- 4.CONTACT PIN:BRAS 0.7t  
SILVER PLATED
- 5.RIVET:AL NICKEL PLATED

3P 180°	5P 180°	5P 240°	6P 240°	7P 270°	8P 270°

<b>笙龍實業有限公司</b> SONION INDUSTRIAL CO., LTD.	
TOLERANCES	PART NUMBER
.x ± 0.1 .xxx ± /	54000 SERIES
.xx ± 0.05 ANGLES /	
mm SCALE /	DESCRIPTION
DRAFT W.RAY 0423'99	DIN SOCKET
CHECK JANNE HUNG	REV. A
APPROVAL DANNY HSU	SHEET 1/1