

Bootlace Ferrules



SPECIFICATION:

Temperature range	-40 ... +105 °C
Material	Copper
Insulation material	Polypropylene
Surface material	Tin-Plated
Termination	Crimp



UL certified: E502427



Colour System

French	German	DIN	Wire Range	Pin Length (L1)	Overall Length (L2)	Terminal Diameter (D1)	Outside Diameter (D2)
	Grey RND 465-00552		22 AWG 0.14 mm ²	6 mm	10 mm	0.7 mm	1.2 mm
Violet RND 465-00565	Light Blue RND 465-00537		24 AWG 0.25 mm ²	6 mm	10 mm	0.75 mm	1.9 mm
RND 465-00899	RND 465-00538		24 AWG 0.25 mm ²	8 mm	12 mm	0.75 mm	1.9 mm
Pink RND 465-00908	Turquoise RND 465-00564		22 AWG 0.34 mm ²	6 mm	10 mm	0.80 mm	1.9 mm
RND 465-00558	RND 465-00563		22 AWG 0.34 mm ²	8 mm	12 mm	0.80 mm	1.9 mm
White RND 465-00566	Orange RND 465-00556	White RND 465-00566	20AWG 0.5 mm ²	8 mm	14 mm	1 mm	2.6 mm
Blue RND 465-00540	White RND 465-00567	Grey RND 465-00546	18 AWG 0.75 mm ²	8 mm	14 mm	1.2 mm	2.8 mm
RND 465-00541	RND 465-00568	RND 465-00883	18 AWG 0.75 mm ²	12 mm	18 mm	1.2 mm	2.8 mm
Red RND 465-00559	Yellow RND 465-00569	Red RND 465-00559	18 AWG 1.0 mm ²	8 mm	14 mm	1.4 mm	3 mm
RND 465-00562	RND 465-00570	RND 465-00562	18 AWG 1.0 mm ²	12 mm	18 mm	1.4 mm	3 mm
Black RND 465-00533	Red RND 465-00561	Black RND 465-00533	16 AWG 1.5 mm ²	8 mm	14 mm	1.7 mm	3.5 mm
RND 465-00531	RND 465-00560	RND 465-00531	16 AWG 1.5 mm ²	10 mm	16 mm	1.7 mm	3.5 mm
RND 465-00534	RND 465-00884	RND 465-00534	16 AWG 1.5 mm ²	18 mm	24 mm	1.7 mm	3.5 mm



Colour System

French	German	DIN	Wire Range	Pin Length (L1)	Overall Length (L2)	Terminal Diameter (D1)	Outside Diameter (D2)
Grey RND 465-00549	Blue RND 465-00542	Blue RND 465-00542	14 AWG 2.5 mm ²	8 mm	14 mm	2.2 mm	4.2 mm
RND 465-00547	RND 465-00539	RND 465-00539	14 AWG 2.5 mm ²	12 mm	18 mm	2.2 mm	4.2 mm
RND 465-00551	RND 465-00885	RND 465-00885	14 AWG 2.5 mm ²	18 mm	24 mm	2.2 mm	4.2 mm
Orange RND 465-00886	Grey RND 465-00548	Grey RND 465-00548	12 AWG 4.0 mm ²	12 mm	20 mm	2.8 mm	4.8 mm
RND 465-00557	RND 465-00550	RND 465-00550	12 AWG 4.0 mm ²	18 mm	26 mm	2.8 mm	4.8 mm
Green RND 465-00544	Black RND 465-00536	Yellow RND 465-00887	10 AWG 6 mm ²	12 mm	20 mm	3.5 mm	6.3 mm
RND 465-00888	RND 465-00532	RND 465-00889	10 AWG 6 mm ²	18 mm	26 mm	3.5 mm	6.3 mm
Brown RND 465-00890	Ivory RND 465-00554	Red RND 465-00891	8 AWG 10 mm ²	12 mm	22 mm	4.5 mm	7.6 mm
RND 465-00892	RND 465-00553	RND 465-00893	8 AWG 10 mm ²	18 mm	28 mm	4.5 mm	7.6 mm
Ivory RND 465-00555	Green RND 465-00545	Blue RND 465-00894	6 AWG 16 mm ²	12 mm	24 mm	5.8 mm	8.8 mm
RND 465-00895	RND 465-00543	RND 465-00896	6 AWG 16 mm ²	18 mm	28 mm	5.8 mm	8.8 mm
Black RND 465-00535	Brown RND 465-00897	Yellow RND 465-00898	4 AWG 25 mm ²	16 mm	30 mm	7.3 mm	11.2 mm
Red RND 465-00900	Beige RND 465-00901	Red RND 465-00900	2 AWG 35 mm ²	16 mm	30 mm	8.3 mm	12.7 mm
Blue RND 465-00902	Olive RND 465-00903	Blue RND 465-00902	1/0 AWG 50 mm ²	20 mm	36 mm	10.3 mm	15 mm
		Yellow RND 465-00904	2/0 AWG 70 mm ²	21 mm	37 mm	13.5 mm	16 mm
		Red RND 465-00905	3/0 AWG 95 mm ²	25 mm	44 mm	14.7 mm	18.5 mm
		Blue RND 465-00906	4/0 AWG 120 mm ²	27 mm	48 mm	16.7 mm	20 mm
		Yellow RND 465-00907	250/3000AWG 150mm ²	32 mm	58 mm	19.5 mm	23 mm