

Crimp Fittings

Press-armaturen


Embouts sertis

Raccordi a graffare

Racores para presión

DLB

DKO Female Swivel, Light Duty, 90° Elbow
 Dichtkopf DKOL, leichte Baureihe, 90° Krümmer
 DKO série L coudé 90°
 Femmina girevole DKOL a 90°, serie leggera
 Hembra loca DKOL acodado a 90°, serie ligera



Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting			mm			mm	mm	mm	mm			mm
1G5DLB3	1S5DLB3	1A5DLB3	M12x1,5		6	5	-3	42,8	25,3	26,5	2,5	14		
1G5DLB4	1S5DLB4	1A5DLB4	M12x1,5		6	6	-4	49,9	26,5	26,5	4,2	14		
1G6DLB4	1S6DLB4	1A6DLB4	M14x1,5		8	6	-4	51,15	27,7	31,0	4,2	17		
1G8DLB5	1S8DLB5	1A8DLB5	M16x1,5		10	8	-5	55,3	31,4	35,5	5,3	19		
1G8DLB6	1S8DLB6	1A8DLB6	M16x1,5		10	10	-6	58,5	33,6	33,5	6,7	19		
1G10DLB5	1S10DLB5	1A10DLB5	M18x1,5		12	8	-5	60,1	36,2	37,5	5,3	22		
1G10DLB6	1S10DLB6	1A10DLB6	M18x1,5		12	10	-6	59,8	34,5	34,2	6,7	22		
1G12DLB8	1S12DLB8	1A12DLB8	M22x1,5		15	12	-8	75,3	45,6	40,0	9,6	27		
	1S10DLB8		M18x1,5		12	12	-8	67,9	38,2	37,2	9,6	22		
1G16DLB10	1S16DLB10	1A16DLB10	M26x1,5		18	16	-10	86,4	57,0	46,5	12,8	32		
1G20DLB12	1S20DLB12	1A20DLB12	M30x2,0		22	19	-12	92,5	62,3	50,7	15,5	36		
1G25DLB16	1S25DLB16	1A25DLB16	M36x2,0		28	25	-16	100,0	66,0	61,0	20,7	41		
1G32DLB20	1S32DLB20	1AP32DLB20*	M45x2,0		35	31	-20	130,0	75,0	79,0	26,6	50		
		1AT32DLB20**	M45x2,0		35	31	-20	130,0	75,0	79,0	26,6	50		
1G40DLB24	1S40DLB24	1A40DLB24	M52x2,0		42	38	-24	152,0	105,7	106,0	32,0	60		

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

Specification subject to change without notice