

F21PL-E

21° 2IN1 RH & MCN STICK NAILER-ST +CASE



Diameter: 2.5 - 3.3mm
Length: 45 - 90mm

Diameter: 4.0 - 4.1mm
Length: 38 - 65mm

Features



Rubber Comfort Grip



Magnesium Housing



Serrated Tip



No-Mar-Tip



Push Button Depth Control



Adjustable Exhaust



Sequential Trip



Anti Slip Bumpers



Compact Nose



Positive Placement Tip



Carry Case



SPECIFICATION

Power type	Pneumatic		Operating pressure	4.80 - 8.30 BAR
Weight	3.70 kg			70.00 - 120.00 PSI
Width	133 mm		Air Consumption Ltr.per shot @ 5.6 bar	2.47
Length	517 mm		Air fitting thread type	1/4 BSP
Height	355 mm		Noise	LPA 1sd 96.70
Magazine capacity (max)	50			LWA 1sd 100.10
PL Series Fasteners:				LPA 1s, 1m 87.10
Diameter (mm)	2.5 (min)	3.3 (max)	Vibration / Uncertainty	2.47 / N/A m/s ²
Length (mm)	45 (min)	90 (max)		
Head (mm)	6.7 (min)	8 (max)		
Collation type	plastic			
Collation angle	21			
MCN Series Fasteners:				
Diameter (mm)	4.0 (min)	4.1 (max)		
Length (mm)	38 (min)	65 (max)		
Head (mm)	8 (min)	8 (max)		
Collation type	plastic			
Collation angle	21			

