


FE-30-P-A-M6

Fibre optics



Product characteristics

Through-beam sensor

M6

Sensing range 300 mm

Connection to fibre optic amplifiers type OIF

Range

Sensing range	OIF: 300 mm
---------------	-------------

Environment

Ambient temperature [°C]	-20...80
--------------------------	----------

Mechanical data

Design	straight
--------	----------

Length [mm]	600
-------------	-----

Min. bending radius [mm]	30
--------------------------	----

Fiber arrangement



Fibre optic

glass

Sensing head

aluminium

Sheathing

PVC; adapter: polyamide

Weight [kg]

0.086

Accessories

Accessories (included)

2 hexagon nuts; M6; stainless steel; 2 tooth lock washers; 1 knurled nut; M30

Remarks

Pack quantity [piece]

1