

**3-conductor ground terminal block**

Item No.: 280-637



3-conductor ground terminal block

**Marking**RoHS ✓  
Compliant**Business data**


Supplier	WAGO
Item no.	280-637
GTIN / EAN	4044918473064
Content	1
Order amount	100
Customer item number	


**Notes****Technical data****Miscellaneous**

Total number of connection points	3
Total number of potentials	1
Color	green-yellow
Ratings according to 1	IEC/EN 60947-7-2
Connection technology (1)	CAGE CLAMP®
Solid sizes 1	0.08 ... 2.5 mm <sup>2</sup> / 28 ... 12 AWG
Fine-stranded wires 1	0.08 ... 2.5 mm <sup>2</sup> / 28 ... 12 AWG
Strip length 1	8 ... 9 mm / 0.31 ... 0.35 in
Note (conductor cross-section)	12 AWG: THHN, THWN
Type of wiring	Front-entry wiring

<b>Technical data</b>	
<i>Design</i>	<i>angled</i>
<i>Marking level</i>	<i>Center marking</i>
<i>Insulating material</i>	<i>Polyamide 66 (PA 66)</i>
<i>Fire load [MJ]</i>	<i>0.109 [MJ]</i>
<i>Weight [g]</i>	<i>11.13 [g]</i>
<i>Width</i>	<i>5 mm / 0.197 in</i>
<i>Height from upper-edge of DIN-rail [mm]</i>	<i>36.5 [mm]</i>
<i>Height from upper-edge of DIN-rail</i>	<i>36.5 mm / 1.437 in</i>
<i>Length</i>	<i>50.5 mm / 1.988 in</i>
<i>Type of mounting</i>	<i>DIN 35 rail</i>

Images & drawings





#### Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.