

Product data sheet

Item No. 91.931.9153.0

Female connector GST15I3S B1 U W WS

Device connectors, snap-in panel mount, jut out version, GST15i3, 4 pole, female, screw connection, 250V/16A, material thickness 0,8 - 1,0 mm, color of coding: white, color of frame: white



Item No.	91.931.9153.0
EAN	4015573869608
Order Unit	100 Piece(s)

Certificates / Approvals



Technical data

General

Rated current	16 A
Rated voltage	250 V
Pollution degree	2
Mechanical coding	Code 1
Rated impulse voltage	4 kV
Interlockable	Yes
Color of coding/ contact carrier	White
Marking of poles	
Color of separate adapter (if present)	White

Connection Data

Connection cross section solid	2.5 mm ²
Cross section solid 2	0.5 mm ²
Connection cross section stranded	2.5 mm ²
Cross section stranded 2	0.5 mm ²
Terminations per pole	1

Model

Model	female
Number of poles	3
Connection type	Screw connection
Connecting thread metric	M3
Angle of plug	Straight
Degree of protection (IP)	IP40
Thickness of housings (electrical device) 2	0.8 mm
Thickness of housings (electrical device)	1 mm
Built-in component	Snap-in/screw-in

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	30.2 mm
Width	22 mm
Height	18.2 mm

