

Clamping heads, round version

ORION®

Application:

Versatile in application, machining centres, all common axial force clamping systems on lathes and vices, measuring machines or pallet clamping.

Execution:

- High-strength rubber/metal connection
- High retention forces
- Corrosion protection coating

| | |
|--|---|
| Art. no. | 22001 229 |
| Brand | ORION |
| Manufacturer Part Number | 22001229 |
| Size | 52 |
| Design | Without stem |
| Profile shape | Round with linear- and transverse grooves |
| Clamping diameter | 37 mm |
| Length | 46 mm |
| Min./max. clamping range diameter | 11-52 mm |
| Gross Weight | 0.770 kg |
| Product Group | 2AO |



EAN

4053625468379