



Sechskant-Abstandshalter - Innen-/ Außengewinde, mit Freistich

P160140



Edelstahl

Artikelnummer	Maße (mm)				Stück/VPE	Artikelnummer	Maße (mm)				Stück/VPE		
	d	S	h2	h1			d	S	h2	h1			
1221450	M2.5	5	5	6	2.5	100	1221490	M4	7	70	8	9	100
1221451	M2.5	5	6	6	4	100	1221491	M4	7	80	8	9	100
1221452	M2.5	5	7	6	4	100	1221492	M5	8	10	8	6	100
1221453	M2.5	5	8	6	5	100	1221493	M5	8	12	8	8	100
1221454	M2.5	5	10	6	6	100	1221494	M5	8	15	8	10	100
1221455	M2.5	5	11	6	6	100	1221495	M5	8	18	8	10	100
1221456	M2.5	5	12	6	7	100	1221496	M5	8	20	8	10	100
1221457	M2.5	5	15	6	10	100	1221497	M5	8	25	8	10	100
1221458	M2.5	5	18	6	10	100	1221498	M5	8	30	8	10	100
1221459	M2.5	5	20	6	10	100	1221499	M5	8	35	8	10	100
1221460	M2.5	5	25	6	10	100	1221500	M5	8	40	8	10	100
1221461	M2.5	5	30	6	10	100	1221501	M5	8	45	8	10	100
1221462	M3	5.5	5	6	2.5	100	1221502	M5	8	50	8	10	100
1221463	M3	5.5	6	6	2.5	100	1221503	M5	8	55	8	10	100
1221464	M3	5.5	8	6	5	100	1221504	M5	8	60	8	10	100
1221465	M3	5.5	10	6	6	100	1221505	M5	8	70	8	10	100
1221466	M3	5.5	12	6	7	100	1221506	M6	10	10	10	5	100
1221467	M3	5.5	15	6	7	100	1221507	M6	10	12	10	7	100
1221468	M3	5.5	18	6	7	100	1221508	M6	10	15	10	10	100
1221469	M3	5.5	20	6	7	100	1221509	M6	10	18	10	12	100
1221470	M3	5.5	25	6	7	100	1221510	M6	10	20	10	12	100
1221471	M3	5.5	30	6	7	100	1221511	M6	10	25	10	12	100
1221472	M3	5.5	35	6	7	100	1221512	M6	10	30	10	12	100
1221473	M3	5.5	40	6	7	100	1221513	M6	10	35	10	12	100
1221474	M3	5.5	50	6	7	100	1221514	M6	10	40	10	12	100
1221475	M4	7	8	8	5	100	1221515	M6	10	50	10	12	100
1221476	M4	7	10	8	6	100	1221516	M6	10	60	10	12	100
1221477	M4	7	12	8	8	100	1221517	M6	10	70	10	12	100
1221478	M4	7	15	8	9	100	1221518	M6	10	80	10	12	100
1221479	M4	7	18	8	9	100	1221519	M6	10	90	10	12	100
1221480	M4	7	20	8	9	100	1221520	M8	13	15	14	10	100
1221481	M4	7	25	8	9	100	1221521	M8	13	18	14	12	100
1221482	M4	7	30	8	9	100	1221522	M8	13	20	14	14	100
1221483	M4	7	35	8	9	100	1221523	M8	13	25	14	14	100
1221484	M4	7	40	8	9	100	1221524	M8	13	30	14	14	100
1221485	M4	7	45	8	9	100	1221525	M8	13	35	14	14	100
1221486	M4	7	50	8	9	100	1221526	M8	13	40	14	14	100
1221487	M4	7	55	8	9	100	1221527	M8	13	50	14	14	100
1221488	M4	7	60	8	9	100	1221528	M8	13	60	14	14	100
1221489	M4	7	65	8	9	100	1221529	M8	13	70	14	14	100


Aluminium

Artikelnummer	Maße (mm)				Stück/VPE	Artikelnummer	Maße (mm)				Stück/VPE		
	d	S	h2	h1			d	S	h2	h1			
1221530	M2.5	5	5	6	2.5	100	1221571	M4	7	70	8	9	100
1221531	M2.5	5	6	6	4	100	1221572	M4	7	80	8	9	100
1221532	M2.5	5	7	6	4	100	1221573	M5	8	10	8	6	100
1221533	M2.5	5	8	6	5	100	1221574	M5	8	12	8	8	100
1221534	M2.5	5	10	6	6	100	1221575	M5	8	15	8	10	100
1221535	M2.5	5	11	6	6	100	1221576	M5	8	18	8	10	100
1221536	M2.5	5	12	6	7	100	1221577	M5	8	20	8	10	100
1221537	M2.5	5	15	6	10	100	1221578	M5	8	25	8	10	100
1221538	M2.5	5	18	6	10	100	1221579	M5	8	30	8	10	100
1221539	M2.5	5	20	6	10	100	1221580	M5	8	35	8	10	100
1221540	M2.5	5	25	6	10	100	1221581	M5	8	40	8	10	100
1221541	M2.5	5	30	6	10	100	1221582	M5	8	45	8	10	100
1221542	M3	5.5	5	6	2.5	100	1221583	M5	8	50	8	10	100
1221543	M3	5.5	6	6	2.5	100	1221584	M5	8	55	8	10	100
1221544	M3	5.5	8	6	5	100	1221585	M5	8	60	8	10	100
1221545	M3	5.5	10	6	6	100	1221586	M5	8	70	8	10	100
1221546	M3	5.5	12	6	7	100	1221587	M6	10	10	10	5	100
1221547	M3	5.5	15	6	7	100	1221588	M6	10	12	10	7	100
1221548	M3	5.5	18	6	7	100	1221589	M6	10	15	10	10	100
1221549	M3	5.5	20	6	7	100	1221590	M6	10	18	10	12	100
1221550	M3	5.5	25	6	7	100	1221591	M6	10	20	10	12	100
1221551	M3	5.5	30	6	7	100	1221592	M6	10	25	10	12	100
1221552	M3	5.5	35	6	7	100	1221593	M6	10	30	10	12	100
1221553	M3	5.5	40	6	7	100	1221594	M6	10	35	10	12	100
1221554	M3	5.5	50	6	7	100	1221595	M6	10	40	10	12	100
1221555	M3	5.5	60	6	7	100	1221596	M6	10	50	10	12	100
1221556	M4	7	8	8	5	100	1221597	M6	10	60	10	12	100
1221557	M4	7	10	8	6	100	1221598	M6	10	70	10	12	100
1221558	M4	7	12	8	8	100	1221599	M6	10	80	10	12	100
1221559	M4	7	15	8	9	100	1221600	M6	10	90	10	12	100
1221560	M4	7	18	8	9	100	1221601	M8	13	15	14	10	100
1221561	M4	7	20	8	9	100	1221602	M8	13	18	14	12	100
1221562	M4	7	25	8	9	100	1221603	M8	13	20	14	14	100
1221563	M4	7	30	8	9	100	1221604	M8	13	25	14	14	100
1221564	M4	7	35	8	9	100	1221605	M8	13	30	14	14	100
1221565	M4	7	40	8	9	100	1221606	M8	13	35	14	14	100
1221566	M4	7	45	8	9	100	1221607	M8	13	40	14	14	100
1221567	M4	7	50	8	9	100	1221608	M8	13	50	14	14	100
1221568	M4	7	55	8	9	100	1221609	M8	13	60	14	14	100
1221569	M4	7	60	8	9	100	1221610	M8	13	70	14	14	100
1221570	M4	7	65	8	9	100							

Sechskant-Abstandshalter - Sub-D, mit Freistich

P160140

Messing vernickelt



Artikelnummer	Maße (mm)						Stück/VPE
	d	d1	S	h1	Min.h	h2	
1221611	4NC	4NC	5	6	3	5	100
1221612	4NC	4NC	5	8	3	5	100
1221613	4NC	4NC	5	12	3	5	100
1221614	4NC	M3	5	6	3	5	100
1221615	4NC	M3	5	8	3	5	100
1221616	M3	4NC	5	6	3	5	100
1221617	M3	4NC	5	8	3	5	100
1221618	M3	4NC	5	12	3	5	100

