



Impedance	50Ω
Frequency range	0-3 GHz
VSWR (straight connectors)	< 1.22 typ
Insulation resistance	≥ 5 × 10 ¹¹ MΩ
Center contact resistance	≤ 10.0 mΩ
Outer contact resistance	< 5.0 mΩ
Test voltage	1000V rms
Working voltage	500 V rms
Insertion loss(dB)	< 0.1dB max/100Hz typ

No.	DESCRIPTION	MATERIAL	FINISH
1	BODY	BRASS	NICKEL
2	CONTACT	BRASS	GOLD
3	INSULATOR	DELTRIN	WHITE
4	SHELL	BRASS	NICKEL