

SA-200 - Amplifier



Universal stereo amplifier

- Silent operation due to fanless cooling concept
- Stereo line input
- Speaker connection via terminal strip
- LEDs for indicating overload (clip)
- Volume control
- 482 mm (19") rack installation, 1 RS, with supplied mounting brackets

Technical Data

Channels	: 2
Zones	: -
Power rating	: -
Power rating at 2 Ohm	: -
Power rating at 4 Ohm	: 2 x 50 W
Power rating at 8 Ohm	: 2 x 30 W
Power rating at 100 V	: -
Power rating with 4 Ohm bridged operation	: -
Power rating with 8 Ohm bridged operation	: -
Peak music power output (P _{MAX})	: 2 x 100 W
Inputs	: 420 mV/6 k Ohm
Frequency range	: 20-20,000 Hz
Crossover network	: -
Crossover frequency	: -
Integrated limiter	: -
Equalizer bass	: -
Equalizer midrange	: -
Equalizer treble	: -
S/N ratio	: > 83 dB
Crosstalk attenuation	: -
THD	: -
Power supply	: ~ 230 V/50 Hz/210 VA
Mains voltage	: ~ 230 V
Mains frequency	: 50 Hz
Power consumption, operation	: 210 VA
Power consumption, standby	: -
Standby current	: -
Alternative operating voltage	: -
Alternative power supply	: -
Admiss. ambient temp.	: 0-40 °C
Dimensions	: 431 x 55 x 255 mm
Width	: 431 mm
Height	: 55 mm
Depth	: 255 mm
Rack spaces, RS	: 1



Weight : 4.6 kg
Connections : line: RCA L/R
 speaker: spring-load. speaker term.