

LEITFÄHIGE VERSANDBOXEN MIT SCHNAPPVERSCHLUSS UND SCHARNIER ODER MIT STÜLPDECKEL



Art.-Nr.	V20-200 ESD	V20-201 ESD	V20-202 ESD	V20-203 ESD	V20-204 ESD	V20-205 ESD
Innenmaße	34 x 34 x 8	58 x 42 x 10	68 x 50 x 13	95 x 70 x 17	115 x 85 x 26	138 x 102 x 30



Art.-Nr.	V 3-12-6-6-10-10*	V 3-18-6-6-10-10*	V 3-30-6-6-10-10*	V 3-40-6-6-10-10*
Innenmaße	50 x 30 x 16	57 x 36 x 17	73 x 42 x 17	80 x 50 x 27



Art.-Nr.	V 1-11-6-6-10-10 26 Ø x 17,5 mm Stülpd.	Art.-Nr.	V 6-4-6-6-10-10	Art.-Nr.	V 3-10-6-6-10-10	V 3-37-6-6-10-10
Art.-Nr.	V 1-12-6-6-10 26 Ø x 13 mm Stülpdeckel		6 Fächer je 19 x 15 x 5 innen		49,5 x 39,5 x 5	75 x 75 x 27
Art.-Nr.	V 2-101-6-6-10-10 52 Ø x 40 mm Schraubd.	Art.-Nr.	V 6-5-6-6-10-10	Art.-Nr.	V 3-53-6-6-10-10	V 3-54-6-6-10-10
Art.-Nr.	V 2-102-6-6-10-10 52 Ø x 67 mm Schraubd.		12 Fächer je 25 x 10 x 10 innen		102 x 25 x 10	102 x 85 x 47



Stapeldosen, Stülpdeckel

Art.-Nr.	V 3-16-6-6-10-10 55 x 55 x 25/16 innen
Art.-Nr.	V 3-17-6-6-10-10 55 x 55 x 35/26 innen
Art.-Nr.	V 3-59-6-6-10-10 115 x 55 x 35/26 innen
Art.-Nr.	V 3-60-6-6-10-10 115 x 55 x 55/46 innen
Art.-Nr.	V 3-61-6-6-10-10 115 x 115 x 55/46 innen



Stapeldosen, Scharnierdeckel

EGB-Schaumstoffeinlagen auf Anfrage

Art.-Nr.	V 8-1-6-6-10-10 75 x 50 x 33 innen
Art.-Nr.	V 8-2-6-6-10-10 75 x 50 x 45 innen
Art.-Nr.	V 8-5-6-6-10-10 106 x 75 x 46 innen
Art.-Nr.	V 8-7-6-6-10-10 156 x 106 x 46 innen



Liastat-Scharnierboxen

Art.-Nr.	V 20-29-6-10 130 x 80 x 14 innen
Art.-Nr.	V 20-30-6-10 130 x 80 x 30 innen
Art.-Nr.	V 20-31-6-10 130 x 80 x 50 innen
Art.-Nr.	V 20-32-6-10 178 x 133 x 78 innen
Art.-Nr.	V 20-33-6-10 221 x 121 x 55 innen




Art.-Nr. **V 8-8-6-6-10-10**

Innenmaße 183 x 108 x 30



Art.-Nr. **V 8-9 SCH + V-6-6-10-10**

Innenmaße 196 x 136 x 49 (Außenmaße 203 x 152 x 53)



Art.-Nr. **V 8-15-6-6-10-10**

Innenmaße 220 x 130 x 35



Art.-Nr. **V 8-14 SCH + V-6-6-10-10**

Außenmaße 295 x 175 x 20

Innenmaße 292 x 160 x 16



Art.-Nr. **V 9-40 SCH + V-6-6-10-10**

Außenmaße 295 x 175 x 20

Innenmaße 73 x 42 x 17



Art.-Nr. **V 8-12 SCH + V-6-6-10-10**

Außenmaße 295 x 175 x 42

Innenmaße 288 x 157 x 38