

Forked clamps

With round clamping face



Version:

- Heat-treated steel
- Painted
- With round clamping face



Art. no.	26130 060
Slot width	18 mm
Length	200 mm
Suitable cheese-head screw DIN 912	M16, M18
Clamping shoe height	30 mm
Clamping shoe width	50 mm
Diameter	24 mm
Length 2	55 mm
Length 3	36 mm
DIN	6315

EAN-Code

4020772070748