

T-slot bolts



Application:

For clamping workpieces on machine tables.

Version:

- Tempered
- Rolled thread
- Forged
- With milled groove guide
- M8 to M12, strength class 10.9
- M16 to M24, strength class 8.8
- DIN 787



Art. no.	26200 345
DIN	787
Thread dimension	M12
Groove width	12 mm
Length excluding head	160 mm
Outer diameter	11.7 mm
Thread length	100 mm
Length of head	18 mm
Head height	7 mm

EAN-Code

4020772081508